

JUMBO PA12



TECHNICAL DATA

PA Corrugated tubes

Temperature range	-40°C to +120°C short term up to +150°C
Capacity/100mm	approx. 700, 800 N

■ STRUCTURE

- Material: modified Polyamide (PA) 12
- Flammability acc. to UL 94 (V0)

■ PROPERTIES

- halogen-free
- cadmium-free

- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Robotics
- Handling systems
- Vehicle construction
- Drag chains
- Oversize corrugated tubes
Cable protection tube for heavy-duty applications

■ NOTES

- Suitable connection glands:
JUMBO gland

Suitable for nominal size	Inner Ø mm	Outer Ø mm, approx.	Bending radius mm	Packaging unit (in m)	grey	black
					Part no.	Part no.
70.0	66.5	79.2	200.0	10	920378	920380
95.0	91.0	106.0	265.0	10	920379	920381