

JUMBO PUR



TECHNICAL DATA

PUR-corrugated tube

Temperature range -40°C to +125°C
short term up to +140°C

Capacity/100mm approx. 500, 800 N

■ STRUCTURE

- Material: modified Polyurethane (PUR)
- Flammability acc. to UL 94 (HB)

■ PROPERTIES

- halogen-free
- cadmium-free

- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Robots
- Handling systems
- Vehicle construction
- Drag chains
- Oversize corrugated tubes
- Cable protection tube for maximum duty robot applications
- Lowest reset quality
- High abrasion resistance

■ NOTES

- Suitable connection glands:
JUMBO gland

Suitable for nominal size	Inner Ø mm	Outer Ø mm, approx.	Bending radius mm	Packaging unit (in m)	black Part no.
70.0	66.5	79.2	160.0	10	920382
95.0	91.0	106.0	210.0	10	920383