

HELUcond PA6-UL



TECHNICAL DATA	
PA Corrugated tubes	
Temperature range	-40°C to +140°C short term up to +160°C
Capacity/100mm	approx. 750 N (NW: 16 / 17)

- STRUCTURE**
- Material: modified Polyamide (PA) 6
 - Flammability acc. to UL 94 (V0)

- PROPERTIES**
- halogen-free
 - cadmium-free

resistant to: fuels, mineral oils, greases, weak bases, weak acids

- APPLICATION**
- Machine and plant construction
 - Robotics
 - Automation technology
 - Vehicle construction and shipbuilding
 - Railway technology
 - Installation technology
 - Control cabinet construction
 - Heavy-duty cable protection tube for heavy-duty mechanical applications

- NOTES**
- Fine or coarse profile. UL recognized / UR from trade size 12.0
 - Suitable connection glands: HELUquick, HSSV.

PA6-UL-F

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
7.5	6.7	10.0	50	920384	920394
10.0	9.8	13.0	50	920385	920395
12.0	12.0	15.8	50	920386	920396
17.0	16.8	21.0	50	920387	920397
23.0	22.9	28.5	50	920388	920398

PA6-UL-B

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
16.0	15.9	21.0	50	920389	920399
21.0	21.7	28.2	50	920390	920400
29.0	27.9	34.2	25	920391	920401
36.0	35.5	42.3	25	920392	920402
48.0	47.5	54.5	25	920393	920403

10.04.2024 / We reserve the right to make technical changes; the imprint in the image is purely exemplary