

HSSV IP68 straight



TECHNICAL DATA

Quick-insert corrugated tubes conduit gland - straight

Temperature range -40°C to +110°C
Protection class IP 68

STRUCTURE

- Material: Polyamide (PA) 6

PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- Quick-insert glands for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

NOTES

- Interior seal made of TPE.
Threaded connection: metric to EN 60423
Each unit includes 1 safety opener

metric thread

Size	Suitable for nominal size	Thread length mm	Spanner size mm	Packaging unit (in pc.)	grey	black
					Part no.	Part no.
M12 x 1.5	10.0	8.9	19	50	920404	920413
M16 x 1.5	10.0	9.3	19	50	920405	920414
M16 x 1.5	12.0	8.6	21	50	920406	920415
M20 x 1.5	16.0 / 17.0	13.0	27	50	920407	920416
M25 x 1.5	21.0 / 23.0	14.3	36	50	920408	920417
M32 x 1.5	29.0	14.2	40	25	920409	920418
M40 x 1.5	36.0 / 37.0	15.0	50	25	920410	920419
M50 x 1.5	48.0 / 50.0	15.5	65	10	920411	920420
M63 x 1.5	48.0 / 50.0	15.5	65	10	920412	920421