

HSSV IP68 straight



TECHNICAL DATA

Quick-insert corrugated tubes conduit gland - straight

Temperature range -40°C to +110°C
Protection class IP 68

■ STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

■ PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- Quick-insert glands for a reliable, quick connection.
Suitable for parallel-coiled HELUcond protection tubes.

■ NOTES

- Interior seal made of TPE.
Threaded connection:
metric to EN 60423
Each unit includes 1 safety opener

metric thread

Size	Suitable for nominal size	Thread length mm	Spanner size mm	Packaging unit (in pc.)	grey	black
					Part no.	Part no.
M12 x 1.50	10.00	8.9	19	50	920404	920413
M16 x 1.50	10.00	9.3	19	50	920405	920414
M16 x 1.50	12.00	8.6	21	50	920406	920415
M20 x 1.50	16.00 / 17.00	13.0	27	50	920407	920416
M25 x 1.50	21.00 / 23.00	14.3	36	50	920408	920417
M32 x 1.50	29.00	14.2	40	25	920409	920418
M40 x 1.50	36.00 / 37.00	15.0	50	25	920410	920419
M50 x 1.50	48.00 / 50.00	15.5	65	10	920411	920420
M63 x 1.50	48.00 / 50.00	15.5	65	10	920412	920421