

# HSSV-KF



TECHNICAL DATA	
<b>PA folding flange</b>	
<b>Temperature range</b>	-40°C to +110°C short term up to +140°C
<b>Protection class</b>	IP 65

- resistant to: fuels, mineral oils, greases, weak bases, weak acids

- STRUCTURE**
- Material: Polyamide (PA) 6
  - Flammability acc. to UL 94 (V0)

- APPLICATION**
- Opening flange angle for connection glands or cable glands. Flange angle opened to enable simple insertion of pre-assembled cables. Highly stable.

- PROPERTIES**
- halogen-free
  - phosphor-free
  - cadmium-free
  - easy to assemble, time and cost savings

- NOTES**
- UR-tested Dimensions  
Threaded connection: metric to EN 45545-2:2016 3x HL
  - Legend:  
Dimensions  
TD - Thread Diameter  
H - Height  
W - Width  
L - Length

**metric thread**

Size	Height mm	Width mm	Length mm	Packaging unit (in pc.)	grey	black (RAL 9005)
					Part no.	Part no.
M16 x 1.5	35	47.0	49.0	10	<b>920507</b>	<b>920513</b>
M20 x 1.5	35	47.0	49.0	10	<b>920508</b>	<b>920514</b>
M25 x 1.5	44	65.0	69.0	10	<b>920509</b>	<b>920515</b>
M32 x 1.5	55	78.0	90.0	10	<b>920510</b>	<b>920516</b>
M40 x 1.5	66	94.0	99.0	10	<b>920511</b>	<b>920517</b>
M50 x 1.5	76	101.0	116.0	10	<b>920512</b>	<b>920518</b>