

STK-PA



TECHNICAL DATA

PA cable gland acc. to DIN 46320

Temperature range -30°C to +80°C
Protection class IP 54

■ STRUCTURE

- Material: Polyamide (PA)
- Seal: Natural rubber (NR)

■ PROPERTIES

- halogen-free
- phosphor-free
- silicone-free
- cadmium-free

■ TESTS

- Test standard EN 62444

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

■ NOTES

- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length
SZ - Spanner Size

metric thread

Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)	grey (RAL 7035) Part no.
M12 x 1.5	5.0 - 8.0	11.0	19	50	92819
M16 x 1.5	7.0 - 9.0	11.0	19	50	92820
M20 x 1.5	8.0 - 12.0	11.0	24	50	92821
M25 x 1.5	11.0 - 14.0	11.0	27	50	92823
M25 x 1.5	13.0 - 17.0	11.0	32	50	92824
M32 x 1.5	18.0 - 26.0	11.0	42	10	92825
M40 x 1.5	23.0 - 26.0	11.0	42	10	92826
M50 x 1.5	25.0 - 33.0	11.0	53	10	92827
M50 x 1.5	32.0 - 40.0	11.0	60	5	92828
M63 x 1.5	38.0 - 44.0	11.0	65	5	92829