

MSVM-S medium voltage straight-through joint heat-shrinking type

triple core



MSVM-S

Centre tension transition sleeve for connecting all 3-core plastic power cables with external conductor layer up to 18/30(36)kV. For connecting cables with differing cross-sections, conductor materials and cable designs with regard to external conductor layer and sheathing. Special solutions enable a 3-core plastic power cable to be connected to 3 single-core plastic power cables.

Properties

- safe field effect
- simple assembly
- large cross-sections
- unlimited conductivity
- immediately operational

Scope of delivery

- Packing unit: 1
- two suspensible silicon control elements
- Field effect filler tape (blue)
- thick-walled heat shrink-on tube
- copper fabric shielding
- heat shrink-on tube as an outside protection
- assembly instruction

triple core

Part no.	Type	Nominal voltage U _o /U(U _m)	Cross-section mm ²	Diameter from - to mm	Unit	Net EUR/item at a purchase of		
						1	2 - 5	6 - 10
93135	MSVM-S12/3	6/10kV	3x 10,0 - 3x 25,0	13,2 - 20,0	1	o. r.	o. r.	o. r.
93136	MSVM-S12/3	6/10kV	3x 35,0 - 3x 95,0	18,2 - 25,0	1	o. r.	o. r.	o. r.
93137	MSVM-S12/3	6/10kV	3x 95,0 - 3x 240,0	20,9 - 35,0	1	o. r.	o. r.	o. r.
93142	MSVM-S24/3	12/20kV	3x 10,0 - 3x 35,0	13,2 - 15,0	1	o. r.	o. r.	o. r.
93143	MSVM-S24/3	12/20kV	3x 50,0 - 3x 150,0	18,2 - 25,0	1	o. r.	o. r.	o. r.
93144	MSVM-S24/3	12/20kV	3x 70,0 - 3x 240,0	20,9 - 30,0	1	o. r.	o. r.	o. r.
93145	MSVM-S24/3	12/20kV	3x 150,0 - 3x 300,0	24,2 - 35,0	1	o. r.	o. r.	o. r.
93186	MSVM-S36/3	18/30kV	3x 35,0 - 3x 70,0	20,9 - 18,0	1	o. r.	o. r.	o. r.
93187	MSVM-S36/3	18/30kV	3x 50,0 - 3x 150,0	24,2 - 25,0	1	o. r.	o. r.	o. r.
93188	MSVM-S36/3	18/30kV	3x 150,0 - 3x 300,0	28,6 - 35,0	1	o. r.	o. r.	o. r.

triple core - special solutions

Part no.	Type	Nominal voltage U _o /U(U _m)	Cross-section mm ²	Diameter from - to mm	Unit	Net EUR/item at a purchase of		
						1	2 - 5	6 - 10
93138	MSVM-S12/3 S	6/10kV	3x 35,0 - 3x 70,0	13,2 - 20,0	1	o. r.	o. r.	o. r.
93139	MSVM-S12/3 S	6/10kV	3x 95,0 - 3x 150,0	18,2 - 25,0	1	o. r.	o. r.	o. r.
93140	MSVM-S12/3 S	6/10kV	3x 185,0 - 3x 300,0	20,9 - 35,0	1	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request