



TECHNICAL DATA

Nickel plated brass strain relief

Temperature range up to +200°C

■ STRUCTURE

- Material: Brass, nickel plated
- with female thread

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For relieving strain on lines where protection tubes are used.

■ NOTES

- Legend:
Dimensions
SI - Size of the internal thread
TL - Thread Length
SZ - Spanner Size
H - Height

PG thread – female

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
94240	PG 7	7.0	16	100
94241	PG 9	7.0	19	100
94242	PG 11	7.0	22	100
94244	PG 16	7.0	26	50

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
94245	PG 21	10.0	33	50
94246	PG 29	10.0	42	25
94247	PG 36	10.0	52	10