

# MfF VASMI - straight-through joint for telephone cable



## MfF

Connection and branch sleeve for telecommunication cables. For connecting telecommunication cables and producing cable branches for telecommunication cables.

## Application

- Outdoors
- Indoors
- Underground
- Water

## Properties

- high electrical insulation values
- water-tight and moisture-protected
- good mechanical strength
- highly resistant to UV rays, earth alkalis and chemical influences
- with temperature indicator colour
- suitable for cut and uncut cables
- dismantlable
- unrestricted storage

## Scope of delivery

- shielding connection conductor with special clamp
- desiccant
- protection inlay
- flame protection film
- shrink-on sleeve
- insulating band
- cleaning agent
- sanding
- assembly instruction

Part no.	Type	Length mm	Cable Ø from - to mm	Converter-fed with core connectors 0,4 mm no. of twin-cores	Converter-fed with core connectors 0,6 mm no. of twin-cores	Converter-fed with core connectors 0,8 mm no. of twin-cores	Net EUR/item at a purchase of		
							1	2 - 5	6 - 10
94330	VASMI 1 SRT	330	8,0 - 35,0	30	20	10	o. r.	o. r.	o. r.
94331	VASMI 1/L SRT	390	8,0 - 35,0	70	40	20	o. r.	o. r.	o. r.
94332	VASMI 2 SRT	380	15,0 - 55,0	100	50	30	o. r.	o. r.	o. r.
94333	VASMI 2/L SRT	450	15,0 - 55,0	150	100	50	o. r.	o. r.	o. r.
94334	VASMI 3 SRT	400	25,0 - 68,0	150	100	70	o. r.	o. r.	o. r.
94335	VASMI 3/L SRT	500	25,0 - 68,0	200	200	100	o. r.	o. r.	o. r.
94336	VASMI 4 SRT	430	28,0 - 94,0	200	200	150	o. r.	o. r.	o. r.
94337	VASMI 5 SRT	600	28,0 - 94,0	400	300	200	o. r.	o. r.	o. r.
94338	VASMI 6 SRT	725	34,0 - 101,0	600	500	300	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request