

# SH, SHV



**TECHNICAL DATA**

**Corrugated tubes holder**

**Temperature range** -40°C to +105°C

- STRUCTURE**
- Material: Polyamide (PA) 6
  - Flammability acc. to UL 94 (V2)

- PROPERTIES**
- halogen-free
  - resistant to: fuels, mineral oils, greases, weak bases, weak acids

- APPLICATION**
- Machine and plant construction
  - Robotics
  - Automation technology
  - Vehicle construction and shipbuilding
  - Railway technology
  - Installation technology
  - Control cabinet construction
  - System holder for HELUcond protection tubes. Universal system holder with optional clips for extreme loads.
- Quick assembly through single-hole fastening.

## SH holder

Suitable for nominal size	Width mm	Height mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
7.00	20.0	18	100	<b>94663</b>	<b>99270</b>
10.00	20.0	23	100	<b>94664</b>	<b>99271</b>
12.00	22.0	26	50	<b>94665</b>	<b>99272</b>
14.00	28.0	33	50	<b>920323</b>	<b>920324</b>
17.00	28.0	33	50	<b>94666</b>	<b>99273</b>
23.00	35.0	40	50	<b>94667</b>	<b>99274</b>
29.00	43.0	45	30	<b>94668</b>	<b>99275</b>
36.00	54.0	53	20	<b>94669</b>	<b>99276</b>
48.00	68.0	66	20	<b>94670</b>	<b>99277</b>

## SHV holder with rotary protection

Suitable for nominal size	Width mm	Height mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
16.00 / 17.00	28.0	33	50	<b>920325</b>	<b>920330</b>

# SH, SHV

Suitable for nominal size	Width mm	Height mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
21.00 / 23.00	35.0	40	50	<b>920326</b>	<b>920331</b>
29.00	43.0	45	30	<b>920327</b>	<b>920332</b>
36.00 / 37.00	54.0	53	20	<b>920328</b>	<b>920333</b>
48.00 / 50.00	68.0	66	20	<b>920329</b>	<b>920334</b>