

HGP



TECHNICAL DATA

Polyester braided hose

Temperature range -50°C to +150°C
short term up to +220°C

■ STRUCTURE

- Material: Polyester
- Axially compressible

■ PROPERTIES

- halogen-free

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- for bundling
- for the mechanical protection of electrical cables and lines

Inner-Ø min. mm	Inner-Ø max. mm	Packaging unit (in m)	grey	black
			Part no.	Part no.
1.0	5.0	100	94900	98136
2.0	7.0	100	94901	98137
3.0	9.0	100	94902	98138
4.0	11.0	100	94903	98139
5.0	12.0	100	94904	98140
7.0	15.0	100	94905	98141
8.0	17.0	50	94906	98142
10.0	20.0	50	94907	98143
14.0	26.0	25	94908	98144
18.0	34.0	25	94909	98145
20.0	40.0	25	94910	98146
30.0	50.0	25	94911	98147
40.0	66.0	25	94912	98148