



TECHNICAL DATA

Protection tube

Temperature range -25°C to +80°C
short term up to +100°C

Protection class IP 67 / IP 66

■ STRUCTURE

- Outer sheath material: Polyolefin
- reinforced, galvanised and spiral wound steel band
- with latched profile
- continuous cord seal
- extruded plastic sheath

■ PROPERTIES

- lead-free
- low smoke development

■ APPLICATION

- Due to the complex construction method, the plastic sheath and internal tube flush together.

■ NOTES

- Suitable connection glands:
LT-straight, LT-elbow 45° and 90°
CV Compact straight, CV Compact elbow 45° and 90°

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	black Part no.
5/16	10.1	14.4	30	94988
3/8	12.6	17.8	30	94989
1/2	16.0	21.1	30	94990
3/4	21.0	26.4	30	94991
1	26.5	33.1	30	94992
1 1/4	35.1	41.8	15	94993