



TECHNICAL DATA

Steel interior socket

Temperature range -55°C to +300°C
Protection class IP 67

■ STRUCTURE

| Part no. | Suitable for tube outer Ø mm | Weight kg, approx. | Packaging unit (in pc.) |
|----------|------------------------------|--------------------|-------------------------|
| 96839 | 17.8 | 1.30 | 50 |
| 97480 | 21.1 | 1.30 | 25 |
| 96580 | 26.4 | 1.40 | 25 |
| 96803 | 33.1 | 1.80 | 25 |
| 96880 | 41.8 | 2.00 | 5 |

- Material: steel galvanized

■ APPLICATION

- For plastic-coated metal protection tubes type Anaconda.

■ NOTES

- Suitable to LT glands

| Part no. | Suitable for tube outer Ø mm | Weight kg, approx. | Packaging unit (in pc.) |
|----------|------------------------------|--------------------|-------------------------|
| 98364 | 47.8 | 2.40 | 5 |
| 905027 | 59.9 | 2.80 | 5 |
| 905028 | 72.6 | 6.40 | 5 |
| 905029 | 88.4 | 7.20 | 5 |
| 905030 | 113.8 | 7.60 | 1 |