



## TECHNICAL DATA

Screening braided hose and interference braided hose

Temperature range -50°C to +250°C

### ■ STRUCTURE

- Material: steel tinned

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- for bundling
- for the mechanical protection of electrical cables and lines

### ■ NOTES

- Also available in 10m lengths.

Part no.	Inner-Ø min. mm	Inner-Ø max. mm	Packaging unit (in m)
97197	5.0	12.0	100
97199	8.0	17.0	50
97200	12.0	22.0	50

Part no.	Inner-Ø min. mm	Inner-Ø max. mm	Packaging unit (in m)
97202	16.0	27.0	50
96561	20.0	35.0	25