



TECHNICAL DATA

Screening braided hose and interference braided hose

Temperature range -50°C to +250°C

■ STRUCTURE

- Material: copper tinned
- Axially compressible

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- for bundling
- for the mechanical protection of electrical cables and lines

■ NOTES

- Also available in 10m lengths.

Part no.	Inner-Ø min. mm	Inner-Ø max. mm	Packaging unit (in m)
97397	5.0	12.0	100
97399	8.0	17.0	50
97400	12.0	22.0	50

Part no.	Inner-Ø min. mm	Inner-Ø max. mm	Packaging unit (in m)
97402	16.0	27.0	50
97403	20.0	35.0	25