

HELUcond CO-PP



TECHNICAL DATA

PP-corrugated tubes

Temperature range -40°C to +135°C
short term up to +150°C

■ STRUCTURE

- Material: Polypropylene (PP)
- Flammability acc. to UL 94 (HB)

■ PROPERTIES

- halogen-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- The dividable and reclosable cable protection tube for subsequent mechanical protection of the cables.
Trouble-free retrofitting
High mechanical strength
Simple installation of pre-fabricated lines
Repair of existing systems

■ NOTES

- Suitable connection glands: COV

trade size mm	Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Bending radius mm	Packaging unit (in m)	black Part no.
10.0	8.4	13.4	1.75	70.0	50	97496
14.0	12.5	18.5	3.05	95.0	50	97134
20.0	19.2	25.3	4.10	130.0	50	97135
23.0	23.4	30.8	5.90	155.0	50	97205
37.0	31.0	41.4	4.75	205.0	25	96732
45.0	42.7	54.0	5.60	190.0	25	90054
70.0	67.5	79.8	3.55	375.0	10	920180