



## T&B 45° angled

Hose gland for Anaconda protection tubes. The specific construction prevents the tubes becoming deformed during assembly.

## Material

Galvanised steel chromate finish  
Grounding sleeve: Steel  
Seal: Polyamide

## Technical data

Protection class: IP 67

## Application

- Plant and machine construction, Automation and installation technology, Vehicle construction and shipbuilding

### metric thread

Part no.	Type	Size Metric	Suitable for tube ND	Suitable for tube outer Ø mm	Thread length mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
								up to 100	101 - 500	501 - 1000
98180	9340	M16 x 1,5	3/8"	17,8	16,0	28,0	25	o. r.	o. r.	o. r.
98181	9341	M20 x 1,5	3/8"	17,8	16,0	28,0	25	o. r.	o. r.	o. r.
98182	9342	M20 x 1,5	1/2"	21,1	16,0	34,0	25	o. r.	o. r.	o. r.
98183	9343	M25 x 1,5	3/4"	26,4	16,0	42,0	10	o. r.	o. r.	o. r.
98184	9344	M32 x 1,5	1"	33,1	23,0	47,0	5	o. r.	o. r.	o. r.

### PG thread

Part no.	Type	Size PG	Suitable for tube ND	Suitable for tube outer Ø mm	Thread length mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
								up to 100	101 - 500	501 - 1000
90693	7341	11	3/8"	17,8	14,0	29,0	25	o. r.	o. r.	o. r.
90694	7342	13,5	3/8"	17,8	14,0	29,0	25	o. r.	o. r.	o. r.
90695	7343	16	1/2"	21,1	14,0	35,0	25	o. r.	o. r.	o. r.
90696	7344	21	3/4"	26,4	14,0	42,0	5	o. r.	o. r.	o. r.
90697	7345	29	1"	33,1	21,0	47,0	5	o. r.	o. r.	o. r.
90698	7346	36	1 1/4"	41,8	21,0	58,0	5	o. r.	o. r.	o. r.
90699	7347	42	1 1/2"	47,8	21,0	69,0	2	o. r.	o. r.	o. r.
90700	7348	48	2"	59,9	24,0	83,0	1	o. r.	o. r.	o. r.

### NPT thread

Part no.	Type	Size NPT	Suitable for tube ND	Suitable for tube outer Ø mm	Thread length mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
								up to 100	101 - 500	501 - 1000
96739	5341	1/2"	3/8"	17,8	14,0	29,0	25	o. r.	o. r.	o. r.
96208	5342	1/2"	1/2"	21,1	14,0	35,0	25	o. r.	o. r.	o. r.
96209	5343	3/4"	3/4"	26,4	14,0	42,0	10	o. r.	o. r.	o. r.
96210	5344	1"	1"	33,1	19,0	48,0	5	o. r.	o. r.	o. r.
98196	5345	1 1/4"	1 1/4"	41,8	21,0	58,0	5	o. r.	o. r.	o. r.
98197	5346	1 1/2"	1 1/2"	47,8	21,0	69,0	2	o. r.	o. r.	o. r.
96211	5347	2"	2"	59,9	22,0	83,0	1	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request