



## T&B 90° angled

Hose gland for Anaconda protection tubes.  
The specific construction prevents the tubes becoming deformed during assembly.

## Material

Galvanised steel chromate finish  
Grounding sleeve: Steel  
Seal: Polyamide

## Technical data

Protection class: IP 67

## Application

- Plant and machine construction
- Robot construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Control cabinet construction

## metric thread

Part no.	Type	Size Metric	Suitable for tube ND	Suitable for tube outer Ø mm	Thread length mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
								up to 100	101 - 500	501 - 1000
98185	9350	M16 x 1,5	3/8"	17,8	16,0	28,0	25	o. r.	o. r.	o. r.
98186	9351	M20 x 1,5	3/8"	17,8	16,0	28,0	25	o. r.	o. r.	o. r.
98187	9352	M20 x 1,5	1/2"	21,1	16,0	34,0	25	o. r.	o. r.	o. r.
98188	9353	M25 x 1,5	3/4"	26,4	16,0	42,0	10	o. r.	o. r.	o. r.
98189	9354	M32 x 1,5	1"	33,1	23,0	47,0	5	o. r.	o. r.	o. r.

## PG thread

Part no.	Type	Size PG	Suitable for tube ND	Suitable for tube outer Ø mm	Thread length mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
								up to 100	101 - 500	501 - 1000
90701	7351	11	3/8"	17,8	14,0	29,0	25	o. r.	o. r.	o. r.
90702	7352	13,5	3/8"	17,8	14,0	29,0	25	o. r.	o. r.	o. r.
90703	7353	16	1/2"	21,1	14,0	35,0	25	o. r.	o. r.	o. r.
90704	7354	21	3/4"	26,4	14,0	42,0	5	o. r.	o. r.	o. r.
90705	7355	29	1"	33,1	21,0	47,0	5	o. r.	o. r.	o. r.
90706	7356	36	1 1/4"	41,8	21,0	58,0	5	o. r.	o. r.	o. r.
90707	7357	42	1 1/2"	47,8	21,0	69,0	2	o. r.	o. r.	o. r.
90708	7358	48	2"	59,9	24,0	83,0	1	o. r.	o. r.	o. r.

Continuation ►

# T&B conduit gland - 90°



## NPT thread

Part no.	Type	Size NPT	Suitable for tube ND	Suitable for tube outer Ø mm	Thread length mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
								up to 100	101 - 500	501 - 1000
97300	5351	1/2"	3/8"	17,8	14,0	29,0	25	o. r.	o. r.	o. r.
96212	5352	1/2"	1/2"	21,1	14,0	35,0	25	o. r.	o. r.	o. r.
96213	5353	3/4"	3/4"	26,4	14,0	42,0	10	o. r.	o. r.	o. r.
97671	5354	1"	1"	33,1	19,0	48,0	5	o. r.	o. r.	o. r.
98291	5355	1 1/4"	1 1/4"	41,8	21,0	58,0	5	o. r.	o. r.	o. r.
96214	5356	1 1/2"	1 1/2"	47,8	21,0	69,0	5	o. r.	o. r.	o. r.
96215	5357	2"	2"	59,9	22,0	83,0	2	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request