


# EW-PA

## Transition from small to large thread



### TECHNICAL DATA

PA extender

Temperature range -40°C to +100°C

### ■ STRUCTURE

- Material: Polyamide (PA)

### ■ PROPERTIES

- halogen-free
- phosphor-free
- silicone-free
- cadmium-free

### ■ NOTES

- Black on request.
- Legend:  
Dimensions  
TD - Thread Diameter  
SI - Size of the internal thread

### from metric to metric

Size outside	Size inside	Packaging unit (in pc.)	grey (RAL 7035) Part no.
M12 x 1.5	M16 x 1.5	100	<b>98585</b>
M16 x 1.5	M20 x 1.5	100	<b>98586</b>
M20 x 1.5	M25 x 1.5	100	<b>95099</b>
M25 x 1.5	M32 x 1.5	50	<b>98587</b>
M32 x 1.5	M40 x 1.5	50	<b>98588</b>
M40 x 1.5	M50 x 1.5	25	<b>98589</b>

### from PG to PG

Size outside	Size inside	Packaging unit (in pc.)	grey (RAL 7035) Part no.
PG 7	PG 9	100	<b>90076</b>
PG 9	PG 11	100	<b>90077</b>
PG 11	PG 13.5	100	<b>90078</b>
PG 11	PG 16	100	<b>96618</b>
PG 13.5	PG 16	100	<b>90079</b>
PG 16	PG 21	50	<b>90080</b>
PG 21	PG 29	25	<b>90081</b>
PG 29	PG 36	20	<b>90082</b>
PG 36	PG 42	10	<b>90083</b>
PG 42	PG 48	5	<b>90084</b>