

HELUcond PA6-L



TECHNICAL DATA

PA Corrugated tubes

Temperature range	-40°C to +120°C short term up to +150°C
Capacity/100mm	approx. 125 N (NW: 17)

■ STRUCTURE

- Material: modified Polyamide (PA) 6
- Flammability acc. to UL 94 (V2)

■ PROPERTIES

- halogen-free
- phosphor-free

- resistant to: fuels, mineral oils, greases, weak bases, weak acids
- UV resistant

■ APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- for light mechanical stress
- Cable protection tube for weak to medium stress applications

■ NOTES

- Fine profile. Suitable connection glands: HELUquick, HSSV.

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
7.5	6.8	10.0	50	99610	99620
10.0	10.0	12.8	50	99611	99621
12.0	12.5	15.7	50	99612	99622
14.0	14.2	18.5	50	99613	99623
17.0	16.8	21.1	50	99614	99624
23.0	23.4	28.4	50	99615	99625
29.0	29.2	34.5	25	99616	99626
37.0	34.0	42.2	25	99617	99627
50.0	46.0	53.8	25	99618	99628