

SK-M

3:1 with inside adhesive



TECHNICAL DATA

Polyolefin shrink tube 3:1

Temperature range -55°C to +110°C

■ STRUCTURE

- Material: Polyolefin
- with interior adhesive

■ PROPERTIES

- halogen-free
- medium walled

- very good chemical resistance

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- for repairing insulation
- for sealing electrical components
- good protection against impact and abrasion

rods

Inner Ø before shrinkage mm	Wall thickness mm	Inner Ø after shrinkage mm	Packaging unit (in m)	black Part no.
10.2	2.0	3.8	1.22	99788
19.1	2.0	5.6	1.22	99789
27.9	2.0	10.2	1.22	99790
33	2.0	10.2	1.22	99791
38.1	2.0	12.7	1.22	99792
43.2	2.0	12.7	1.22	99793
52.1	2.0	19	1.22	99794
69.9	2.0	25	1.22	99795
88.9	2.4	30	1.22	99796
119.4	2.7	40	1.22	99797
152	2.8	48	1.22	99798
170.2	2.8	58	1.22	99799
228.6	3.0	77	1.22	99678