

Certificate of compliance

with the order 2.1 according to EN 10 204

HELUCHAIN® MULTISPEED® 520-PVC UL/CSA

We confirm that the above mentioned **PVC drag chain cable** is produced **acc. to UL-Std. 758 (AWM) Style 21179, CSA-Std. C22.2 No. 210 - AWM I/II A/B, in alignment with DIN VDE 0285-525-2-51 / DIN EN 50525-2-51** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -5°C to +80°C fixed -30°C to +80°C
Nominal voltage	AC U ₀ /U 600/1000 V UL (AWM) AC 1000 V

TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1
oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
10.01.2025

Date of expiration
31.12.2026

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany