

# Certificate of compliance

with the order 2.1 according to EN 10 204

## HELUCHAIN® MULTISPEED® PWR 520-C-PVC UL/CSA

We confirm that the above mentioned **PVC drag chain cable** is produced **acc. to UL-Std. 758 (AWM) Style 21179, CSA-Std. C22.2 No. 210 - AWM I/II A/B, in alignment with DIN VDE 0285-525-2-51 / DIN EN 50525-2-51** and tested according to DIN EN 50395, DIN EN 50396.

### TECHNICAL DATA

|                          |                                                       |
|--------------------------|-------------------------------------------------------|
| <b>Temperature range</b> | flexible -5°C to +80°C<br>fixed -30°C to +80°C        |
| <b>Nominal voltage</b>   | AC U <sub>0</sub> /U 600/1000 V<br>UL (AWM) AC 1000 V |

### TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1  
oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404

### PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
21.01.2025

**Date of expiration**  
31.12.2026

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany