

Certificate of compliance

with the order 2.1 according to EN 10 204

HELUPOWER® SOLARFLEX®-X RPVU90-AL

TECHNICAL DATA

Temperature range	fixed -40°C to +90°C
Permissible operating temperature of the conductor	+120°C
Nominal voltage	UL (PV) DC 2000 V

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1
flame-retardant acc. to UL VW-1, CSA FT1
smoke density acc. to DIN VDE 0482-1034-1+2 / DIN EN 61034-1+2 / IEC 61034-1+2
UV-resistant acc. to UL Std. 2556, CSA Std. C22.2 No. 2556

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
17.03.2025

Date of expiration
31.12.2027

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany