

HELU KABEL GmbH
Headquarters
Dieselstraße 8-12
71282 Hemmingen
Germany

P +49 7150 9209-0
F +49 7150 81786
techsupport@helukabel.de
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

MULTIFLEX 512[®]-PUR

We confirm that the above mentioned, halogen-free PUR cables for drag chains are produced adapted to DIN VDE 0285-525-2-21 / DIN EN 50525-2-21 and tested according to EN 50396, EN 50395.

- **Temperature range**
 - flexing - 30°C to + 80°C
 - fixed installation - 40°C to + 80°C
- **Nominal voltage** U₀/U 300/500 V

Tests

- oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404
- UV-resistant acc. to DIN EN ISO 4892-2
- weather-resistant acc. to DIN EN ISO 4892-2

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

HELU KABEL GmbH
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam