

# Certificate of compliance

with the order 2.1 according to EN 10 204

## NSHTÖU

We confirm that the above mentioned **Reelable control and connection cable** is produced **acc. to DIN VDE 0250-814** and tested according to DIN EN 50395, DIN EN 50396.

## TECHNICAL DATA

**Temperature range** flexible -25°C to +80°C  
fixed -40°C to +80°C  
**Nominal voltage** AC U<sub>0</sub>/U 600/1000 V

## TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2  
oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404  
certifications and approvals:  
EAC

## PROPERTIES



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

---

**Date of issue**  
05.05.2022

**Date of expiration**  
31.12.2022

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany