

# Certificate of compliance

with the order 2.1 according to EN 10 204

## TRAYCONTROL® 300 TP

### TECHNICAL DATA

<b>Temperature range</b>	flexible +5°C to +50°C fixed -25°C to +105°C
<b>Nominal voltage</b>	AC U 300 V

### TESTS

flame-retardant acc. to CSA FT4  
oil-resistant acc. to UL Std. 13 No. 40, Oil Res I / Oil Res II  
Cold Bend Test acc. to UL Std. 13 No. 22  
Impact Test (-ER) acc. to UL Std. 13 No. 23  
Crushing Test (-ER) acc. to UL Std. 13 No. 24  
Vertical-Tray Flame Test (FT4) CSA-Std. C22.2 No. 2256  
certifications and approvals:  
EAC  
ECOLAB®

### PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
18.08.2025

**Date of expiration**  
31.12.2027

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany