

HELU KABEL GmbH
Headquarters
Dieselstraße 8-12
71282 Hemmingen
Germany

P +49 7150 9209-0
F +49 7150 81786
techsupport@helukabel.de
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

TRAYCONTROL® 500

We confirm that the above mentioned PVC cables, NFPA 79, are produced according to UL-Std. 1277 and UL-Std. 2277.

- **Temperature range**
flexing + 5°C to + 50°C
fixed installation - 25°C to + 90°C
- **Nominal voltage**
TC, MTW, CIC, AWM 600V
WTTC 1000V

Tests

- Flame retardant acc. to CSA FT4

Approvals:

- **UL:**
TC-ER (≥ 18 AWG), 90 °C DRY / WET (TC), PLTC (20 - 12 AWG),
ITC-ER (20 - 12 AWG), MTW, WTTC (≥ 18 AWG), SUN RES, DIR BUR,
OIL RES I/II, Class 1 Div. 2 per NEC Art. 501
- **CSA:**
c(UL) CIC-TC FT4 (≥ 18 AWG), CSA AWM I/II A/B FT4

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

HELU KABEL GmbH
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam