

HELU KABEL GmbH
Headquarters
Dieselstraße 8-12
71282 Hemmingen
Germany

P +49 7150 9209-0
F +49 7150 81786
techsupport@helukabel.de
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

FIVENORM (0,5 mm²/AWG 22 - 120 mm²/AWG 4/0)

We confirm that the above mentioned PVC single cores are produced according to DIN VDE 0285-525-2-31 / DIN EN 50525-2-31, UL-Std. 1063 (MTW), UL AWM Style 10269, CSA TEW, CSA AWM I A/B and tested to EN 50396, EN 50395.

- **Temperature range**

H05V2-K / H07V2-K	flexing	+ 5°C to + 90°C
	fixed installation	- 40°C to + 90°C
UL (AWM)		- 40°C to + 105°C
UL (MTW)		- 40°C to + 90°C
CSA (TEW)		- 40°C to + 105°C
- **Nominal voltage**

H05V2-K	U ₀ /U 300/500 V (≤ 1mm ²)
H07V2-K	U ₀ /U 450/750 V (≥ 1,5mm ²)
UL (AWM)	U 1000 V
UL (MTW)	U 600 V
CSA (TEW)	U 600 V

Test

- flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

HELU KABEL GmbH
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam