

Certificate of compliance

with the order 2.1 according to EN 10 204

TOPFLEX® 304

We confirm that the above mentioned **PVC sheathed single core cable** is produced **acc. to UL-Std. 758 (AWM) Style 1032, CSA-Std. C22.2 No. 210 - AWM I A/B** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -5°C to +90°C fixed -40°C to +90°C
Nominal voltage	AC U ₀ /U 600/1000 V UL (AWM) AC 1000 V

TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, CSA FT1, UL VW-1



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
16.07.2025

Date of expiration
31.12.2027

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany