

Certificate of compliance

with the order 2.1 according to EN 10 204

HELUCONTROL[®] 2516 / 600 GREY / HELUCONTROL[®] 2516 / 600 BLACK

We confirm that the above mentioned **PVC control and connection cable** is produced **acc. to UL-Std. 758 (AWM) Style 2516, CSA-Std. C22.2 No. 210 - AWM I/II A/B** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range flexible -10°C to +105°C
fixed -40°C to +105°C

Nominal voltage UL (AWM) AC 600 V

TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
15.01.2024

Date of expiration
31.12.2025

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany