

Certificate of compliance

with the order 2.1 according to EN 10 204

YELLOWFLEX

We confirm that the above mentioned **Rubber connection cable** is produced **in alignment with DIN VDE 0285-525-2-21 / DIN EN 50525-2-21** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -25°C to +60°C fixed -30°C to +60°C
Permissible operating temperature of the conductor	+60°C
Nominal voltage	AC U ₀ /U 450/750 V

TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2
certifications and approvals:
EAC



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
27.03.2026

Date of expiration
31.12.2028

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helu.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany