

Certificate of compliance

with the order 2.1 according to EN 10 204

THERMFLEX® 180 EWKF-C

We confirm that the above mentioned **Silicone control and connection cable** is produced **in alignment with DIN VDE 0285-525-2-83 / DIN EN 50525-2-83** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -25°C to +180°C fixed -60°C to +180°C
Nominal voltage	AC U ₀ /U 300/500 V

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1
corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2
certifications and approvals:
EAC



Product conforms with Low-Voltage Directive 2014/35/EU

HELUX KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
27.03.2026

Date of expiration
31.12.2028

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helu.com

HELUX KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany