



TECHNICAL DATA

Cable ties with plastic lug

Temperature range -40°C to +85°C

STRUCTURE

- Material: Polyamide (PA) 6.6
- Flammability acc. to UL 94 (V2)

PROPERTIES

- halogen-free
- silicone-free

APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- for directionality and mounting

NOTES

- black: good UV-resistance

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	black	transparent
						Part no.	Part no.
T 2-20	100.0	2.5	24	110	100	90140	90150
T 2-50	200.0	2.5	55	110	100	90141	90151
T 3-35	140.0	3.5	36	200	100	90142	90152
T 3-50	200.0	3.5	55	200	100	90143	90153
T 3-75	280.0	3.5	80	200	100	90144	90154
T 5-100	360.0	4.5	101	280	100	90148	90158
T 5-75	280.0	4.5	76	280	100	90146	90156
T 5-85	200.0	4.5	51	280	100	90147	90157
T 8-100	360.0	7.5	101	650	100	90149	90159
T 9-165	610.0	9.0	177	800	100	96492	96491
T 9-230	762.0	9.0	227	800	100	97223	97219

22.03.2024 / We reserve the right to make technical changes; the imprint in the image is purely exemplary