

HELUquick elbow 90°



TECHNICAL DATA

Corrugated tubes conduit gland

Temperature range -40°C to +120°C
Protection class IP 68

STRUCTURE

- Material: Polyamide (PA) 6

PROPERTIES

- halogen-free
- silicone-free
- cadmium-free
- resistant to: oil, petrol, weak acids, weak bases

APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Quick-insert glands for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

NOTES

- UR-tested
Disassembly without additional opener.
Also available straight and angled 45°.

metric thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
M10 x 1.0	7.5	12.0	50	904805	904835
M12 x 1.5	10.0	10.0	50	904806	904836
M16 x 1.5	10.0	12.0	50	904807	904837
M16 x 1.5	12.0	12.0	50	904808	904838
M20 x 1.5	12.0	13.0	50	904809	904839
M20 x 1.5	17.0	13.0	50	904810	904840
M25 x 1.5	17.0	13.0	50	904811	904841
M25 x 1.5	23.0	13.0	25	904812	904842
M32 x 1.5	23.0	15.0	25	904813	904843
M32 x 1.5	29.0	15.0	10	904814	904844
M40 x 1.5	29.0	15.0	10	904815	904845
M40 x 1.5	37.0	15.0	10	904816	904846
M50 x 1.5	37.0	15.5	10	904817	904847
M50 x 1.5	50.0	15.0	5	904818	904848
M63 x 1.5	50.0	16.0	5	904819	904849