


K plastic spring with PVC sheath



Type K

Type K cable protection tube with integrated hard plastic winding.

Application

- Plant and machine construction
- Automation technology
- Installation technology
- Control cabinet construction

Material

PVC

- silicone-free
- cadmium-free

Note

Suitable connection glands:
USK, LK-I, US and LI

Technical data

Temperature range: -20°C up to +70°C
Temperature range temporary up to +80°C

Part no. grey	Inner Ø mm	Outer Ø mm	Per metres	Net EUR/100 metres at a purchase of		
				up to 100	101 - 500	501 - 1000
91209	10,0	14,0	50	o. r.	o. r.	o. r.
91210	13,0	17,0	50	o. r.	o. r.	o. r.
91211	15,0	19,0	50	o. r.	o. r.	o. r.
91212	16,0	21,0	50	o. r.	o. r.	o. r.
91213	22,0	27,0	50	o. r.	o. r.	o. r.
91214	30,0	36,0	25	o. r.	o. r.	o. r.
91215	38,0	45,0	25	o. r.	o. r.	o. r.
91216	45,0	52,0	25	o. r.	o. r.	o. r.
91217	49,0	56,0	25	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request