


ADI-K



TECHNICAL DATA

Core end sleeves

Temperature range up to +105°C

■ STRUCTURE

- Material: copper
- Surface: galvanic tin plated
- Insulation: Polypropylene (PP)

■ APPLICATION

- The core end sleeve is suitable for short circuit-proof lines. It prevents stripped wires from fanning. The hopper-shaped plastic collar enables them to be pushed easily onto the wires.

■ NOTES

- Legend:
Dimensions
L - Length
l - Length to centre of hole

Part no.	Cross-sec. mm ²	Design	Colour	Colour code	Length mm	Sleeve length mm	Packaging unit (in pc.)
91589	1.5	normal	black	DIN	17.5	8	100
91590	1.5	long	black	DIN	19.5	10	100
91591	2.5	normal	blue	DIN	17.5	8	100
91592	2.5	long	blue	DIN	21.5	12	100
97479	4	normal	grey	DIN	19.5	10	100
91593	6	normal	yellow	DIN	23.0	12	100
91595	10	normal	red	DIN	24.0	12	100
91598	16	normal	blue	DIN	25.5	12	100