

HELUcond PE



TECHNICAL DATA

PE Corrugated tubes

Temperature range	-40°C to +70°C short term up to +90°C
Capacity/100mm	approx. 125 N (NW: 17)

■ STRUCTURE

- Material: modified Polyethylene (PE)
- Flammability acc. to UL 94 (HB)

■ PROPERTIES

- halogen-free
- resistant to: bases

■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- Cable protection tube for weak stress applications.

■ NOTES

- For fine or coarse profiles. Suitable connection glands: HELUquick.

PE-F

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
10.0	9.8	12.7	50	91621	90448
12.0	11.6	15.6	50	90433	90449
17.0	16.3	20.8	50	90435	90451
23.0	22.9	27.9	50	90436	90452
29.0	28.9	34.0	25	90437	90453
37.0	33.5	41.5	25	90438	90454
50.0	45.2	53.4	25	90439	90455

PE-B

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
21.0	21.7	28.2	50	93781	93786
29.0	27.9	34.2	25	93782	93787
36.0	35.5	42.3	25	93783	93788
48.0	47.5	54.5	25	93784	93789