


HSSV elbow 45° plastic



TECHNICAL DATA

Corrugated tubes conduit gland

Temperature range	-40°C to +110°C
Protection class	IP 65

■ STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

■ PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Quick-insert glands for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

■ NOTES

- UR-tested
- Protection classification: IP 66 with outer seal
- Threaded connection: metric to EN 60423
- Each unit includes 1 safety opener. With PG thread on request.

metric thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
M25 x 1.50	21.00 / 23.00	15.5	50	920196	920204
M32 x 1.50	29.00	13.6	25	920197	920205
M40 x 1.50	36.00 / 37.00	15.8	25	920198	920206
M50 x 1.50	48.00 / 50.00	16.3	10	920199	920207
M63 x 1.50	48.00 / 50.00	15.4	10	920200	920208