



TECHNICAL DATA

Steel lug lock cable tie

Temperature range -60°C to +105°C

■ STRUCTURE

- Material: Polyamide (PA) 6.6, heat-stabilised
- Flammability acc. to UL 94 (V2)

■ PROPERTIES

- halogen-free
- silicone-free

■ APPLICATION

- Cable tie with steel lug lock made of corrosion-resistant, non-magnetic steel. This technology enables the cable tie to offer excellent binding properties even under the most rigorous conditions such as heat, cold, humidity etc. and makes it insensitive to vibrations and external influences.

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	transparent Part no.
TYH 23M	92.0	2.4	16	80	1000	97280
TYH 232M	203.0	2.4	50	80	1000	96481
TYH 24M	140.0	3.6	29	130	1000	96577
TYH 242M	208.0	3.6	50	130	1000	98520
TYH 26M	284.0	3.6	76	130	1000	97249
TYH 25M	186.0	4.8	45	220	1000	97213
TYH 253M	290.0	4.8	78	220	1000	98521
TYH 28M	360.0	4.8	102	220	1000	96291
TYH 29M	771.0	6.9	229	530	500	97250
TYH 27M	340.0	7.0	90	540	500	97154
TYH 272M	222.0	7.6	50	540	500	98522