



TECHNICAL DATA

Spiral wound metallic tube

Temperature range -50°C to +250°C
short term up to +220°C

Protection class IP 40

STRUCTURE

- Material: Cold strip acc. to DIN 1624 St 2, Fe/ Zn 3, galvanized
- with steel wire braiding
- with latched profile

PROPERTIES

- high tensile and transverse pressure load rating
- high flexible

APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- Vehicle construction and shipbuilding

NOTES

- Suitable connection glands: MTG-US, MTG-LI

Part no.	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)
97584	7.0	10.0	50
97585	10.0	14.0	50
97586	13.0	17.0	50
97510	15.0	19.0	50
97377	17.0	21.0	50

Part no.	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)
97378	22.0	27.0	50
97379	29.0	36.0	25
96784	38.0	45.0	25
97587	49.0	56.0	25

small pack

Part no.	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)
94920	7.0	10.0	10
94921	10.0	14.0	10
94922	13.0	17.0	10
94923	15.0	19.0	10
94924	17.0	21.0	10

Part no.	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)
94925	22.0	27.0	10
94926	29.0	36.0	10
94927	38.0	45.0	10
94928	49.0	56.0	10