



TECHNICAL DATA

Spiral wound metallic tube

Temperature range	-50°C to +100°C
Protection class	IP 68

■ STRUCTURE

- Material: steel galvanized
- Outer sheath material: Polyurethan (PUR)
- with latched profile

■ PROPERTIES

- halogen-free

- silicone-free
- cadmium-free
- resistant to: oil, greases, petrol
- high tensile and transverse pressure load rating

■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction

■ NOTES

- Suitable connection glands: MTG-US, MTG-LI

Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Packaging unit (in m)	blue Part no.
7.0	10.0	0.07	50	97793
10.0	14.0	0.12	50	97794
13.0	17.0	0.15	50	91131
15.0	19.0	0.20	50	905912
17.0	21.0	0.23	50	94738
22.0	27.0	0.32	50	97941
29.0	36.0	0.56	25	94739
38.0	45.0	0.72	25	94714
49.0	56.0	0.90	25	90399