T-WS

TECHNICAL DATA

Cable ties with plastic lug

Temperature range	-40°C to +85°C short term up to +105°C

STRUCTURE

- Material: Polyamide (PA) 6.6
- Flammability acc. to UL 94 (V2)

PROPERTIES

- halogen-free
- weather-resistant

APPLICATION

- for directionality and mounting
- Outdoor area

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	black Part no.
T-WS 25/100 BK	100.0	2.5	22	80	100	**905525**
T-WS 25/140 BK	145.0	2.5	35	80	100	**905527**
T-WS 25/205 BK	205.0	2.5	50	80	100	**905526**
T-WS 28/330 BK	330.0	2.8	95	110	100	**905528**
T-WS 35/150 BK	150.0	3.5	35	135	100	**905529**
T-WS 35/190 BK	198.0	3.5	50	135	100	**905530**
T-WS 35/290 BK	290.0	3.5	80	135	100	**905531**
T-WS 40/175 BK	175.0	4.0	40	180	100	**905532**
T-WS 46/245 BK	245.0	4.6	65	225	100	**905536**
T-WS 46/200 BK	210.0	4.7	55	355	100	**905533**
T-WS 47/300 BK	305.0	4.7	85	355	100	**905537**
T-WS 46/390 BK	390.0	4.7	110	355	100	**906682**
T-WS 76/225 BK	225.0	7.6	55	535	100	**905542**
T-WS 76/300 BK	300.0	7.6	80	535	100	**905539**
T-WS 76/365 BK	365.0	7.6	100	670	100	**905543**
T-WS 76/380 BK	387.0	7.6	100	535	100	**906683**
T-WS 76/460 BK	460.0	7.6	125	535	100	**905541**
T-WS 76/760 BK	760.0	7.6	225	535	100	**906684**
T-WS 89/530 BK	530.0	8.9	150	780	100	**906686**
T-WS 88/820 BK	820.0	8.9	245	780	100	**906685**
T-WS 132/535 BK	535.0	13.2	150	1115	100	**905546**

13.05.2024 / We reserve the right to make technical changes; the imprint in the image is purely exemplary