

# Patch Cables RJ45 unscreened



Category 6/ Class E



## Type

### Cable

Designation:  
Sheath material:  
Frequency:

## Patch cable unscreened U/UTP PVC, Cat.6

U/UTP 4x2xAWG 24/7 PVC  
PVC  
up to 250 MHz

### Plug

Push-on connector type 1:  
Push-on connector type 2:  
Pin assignment:

RJ45 8(8)  
RJ45 8(8)  
1:1 acc. to TIA/EIA 568 B

### Flame proof

acc. to IEC 60332-1-2

### Norms and standards

HELUKAT® CONNECTING SYSTEMS® system components up to 250 MHz in the of category 6 or EIA/TIA 568 B.

### Preferred types

Part no.	Sheath colour	Length in metres	Unit
<b>803097</b>	grey	0,5	10
<b>803098</b>	grey	1,0	10
<b>803099</b>	grey	2,0	10
<b>803100</b>	grey	3,0	10
<b>803101</b>	grey	5,0	10
<b>803102</b>	grey	7,5	10
<b>803103</b>	grey	10,0	10
<b>803104</b>	grey	15,0	10

Part no.	Sheath colour	Length in metres	Unit
<b>803113</b>	blue	0,5	10
<b>803114</b>	blue	1,0	10
<b>803115</b>	blue	2,0	10
<b>803116</b>	blue	3,0	10
<b>803117</b>	blue	5,0	10
<b>803118</b>	blue	7,5	10
<b>803119</b>	blue	10,0	10
<b>803120</b>	blue	15,0	10

Part no.	Sheath colour	Length in metres	Unit
<b>803121</b>	green	0,5	10
<b>803122</b>	green	1,0	10
<b>803123</b>	green	2,0	10
<b>803124</b>	green	3,0	10
<b>803125</b>	green	5,0	10
<b>803126</b>	green	7,5	10
<b>803127</b>	green	10,0	10
<b>803128</b>	green	15,0	10

Continuation ►

# Patch Cables RJ45 unshielded



Category 6/ Class E

Part no.	Sheath colour	Length in metres	Unit
803105	red	0,5	10
803106	red	1,0	10
803107	red	2,0	10
803108	red	3,0	10
803109	red	5,0	10
803110	red	7,5	10
803111	red	10,0	10
803112	red	15,0	10

Part no.	Sheath colour	Length in metres	Unit
803129	yellow	0,5	10
803130	yellow	1,0	10
803131	yellow	2,0	10
803132	yellow	3,0	10
803133	yellow	5,0	10
803134	yellow	7,5	10
803135	yellow	10,0	10
803136	yellow	15,0	10

Part no.	Sheath colour	Length in metres	Unit
803137	black	0,5	10
803138	black	1,0	10
803139	black	2,0	10
803140	black	3,0	10
803141	black	5,0	10
803142	black	7,5	10
803143	black	10,0	10
803144	black	15,0	10

Dimensions and specifications may be changed without prior notice.

## Options

Naturally, we also offer other lengths, colors and crossover cables on request.