


KMK-PA-MB



TECHNICAL DATA

PA counter nut

Temperature range -40°C to +100°C

STRUCTURE

- Material: Polyamide (PA) 6
- with collar

PROPERTIES

- halogen-free
- phosphor-free
- silicone-free
- cadmium-free

APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- Has a bigger sealing area - sealing with an additional O-ring will be simplified.

NOTES

- Legend:
SZ - Spanner Size
TD - Thread Diameter

metric thread – female

Size	Spanner size mm	Packaging unit (in pc.)	grey	grey	black
			(RAL 7035) Part no.	(RAL 7001) Part no.	(RAL 9005) Part no.
M12 x 1.5	18	100	97816	94260	98163
M16 x 1.5	22	100	97817	94261	98164
M20 x 1.5	26	100	97818	94262	98165
M25 x 1.5	32	100	97819	94263	98166
M32 x 1.5	41	100	97820	94264	98167
M40 x 1.5	50	50	97821	94265	98168
M50 x 1.5	60	50	97822	94266	98169
M63 x 1.5	75	25	97823	94267	98170

PG thread – female

Size	Spanner size mm	Packaging unit (in pc.)	grey	grey	black
			(RAL 7035) Part no.	(RAL 7001) Part no.	(RAL 9005) Part no.
PG 7	19	100	90710	94250	96458
PG 9	22	100	90711	94251	96228
PG 11	24	100	90712	94252	96459

Continued on next page

KMK-PA-MB

Size	Spanner size mm	Packaging unit (in pc.)	grey	grey	black
			(RAL 7035) Part no.	(RAL 7001) Part no.	(RAL 9005) Part no.
PG 13.5	27	100	90713	94253	96460
PG 16	30	100	90714	94254	96461
PG 21	36	100	90715	94255	96176
PG 29	46	50	90716	94256	96177
PG 36	60	25	90717	94257	96462
PG 42	65	25	90718	94258	96463
PG 48	70	25	90719	94259	96464

NPT thread – female

Size	Spanner size mm	Packaging unit (in pc.)	grey	grey	black
			(RAL 7035) Part no.	(RAL 7001) Part no.	(RAL 9005) Part no.
NPT 3/8"	22	100	97317	90870	90875
NPT 1/2"	27	100	97316	90871	90876
NPT 3/4"	33	100	97315	90872	90877
NPT 1"	47	100	98366	-	-
NPT 1"	47	50	-	90873	90878