

Technical data

- Special PUR insulation and sheath adapted to DIN VDE 0250
- Strain bearing support strand
- Temperature range -40°C to +80°C (up to +100°C for short periods)
- Nominal voltage up to 1 mm² U₀/U 300/500 V from 1,5 mm² U₀/U 450/750 V
- Test voltage up to 1 mm² = 2000 V from 1,5 mm² = 2500 V
- **Breakdown voltage** up to 1 mm² = 4000 V from 1,5 mm² = 5000 V
- Insulation resistance min. 20 MOhm x km
- Minimum bending radius 10x cable Ø
- Radiation resistance up to 100x10⁶ cJ/kg (up to 100 Mrad)

Cable structure

- Bare copper-conductor, to
 DIN VDE 0295 cl.6 col.4, extra fine-wire,
 BS 6360 cl.6, IEC 60228 cl.6
- Core insulation of special PUR
- Support core
- Core identification to DIN VDE 0293 (flexible cables)
- Cores stranded in layers with optimal lay-length
- Core wrapping with fleece
- Support braiding of synthetic fibres
- Outer sheath of halogen-free PUR
- Sheath colour orange

Properties

- High flexibility at low temperatures
- Usable for foodstuffs
- Abrasion and tear resistant
- Loadable under torsional stress

Resistant to

- Oils and fats
- Non-alcoholic fuels and kerosene
- Atmospheric influences
- UV-radiation
- Oxygen and ozone
- Microbes and rotting
- Sea and waste water
- Vibrations

Note

- G = with green-yellow conductor
- AWG sizes are approximate equivalent values. The actual cross-section is in mm².

Application

TROMMPUR® has taken the development of the neoprene type cables one step further. It is a robust, all-weather cable, halogen-free, tear and abrasion resistant and suitable for use in drag-chains, in ship docks, on building sites, for conveyor systems, in mining, for tunnels and roadbuilding. For the connecting the ski lift terminal positions to the control unit, surveillance of the joining rods in ski lift cables, as feeder cables for very high currents as for example in pump engineering, mining, locomotive and rail-carriage construction, for oil rig platforms, emergency power generators etc.

C = The product is conformed with the EC Low-Voltage Directive 2006/95/EC.

Part no.	No.cores x cross-sec.	Outer Ø app. mm	Cop. weight	Weight app. kg / km	Breaking strain ca. kp	AWG-No.
	mm²		kg / km		·	
26035	14 G 0,75	16,5	154,0	320,0	250	19
26036	12 G 1	17,5	115,0	300,0	500	18
26037	18 G 1	23,0	173,0	480,0	500	18
26038	3 G 1,5	9,5	43,0	110,0	200	16
26039	5 G 1,5	12,5	72,0	220,0	200	16
26040	7 G 1,5	15,5	101,0	270,0	250	16
26041	12 G 1,5	21,0	173,0	450,0	750	16
26042	18 G 1,5	27,0	259,0	620,0	750	16
26043	24 G 1,5	30,0	346,0	850,0	750	16
26044	30 G 1,5	34,0	533,0	1100,0	750	16
26045	42 G 1,5	40,0	605,0	1600,0	750	16
26046	4 G 2,5	14,0	96,0	250,0	200	14
26047	5 G 2,5	15,0	120,0	280,0	250	14
26048	7 G 2,5	18,0	168,0	360,0	300	14
26049	12 G 2,5	25,0	288,0	740,0	750	14
26050	24 G 2,5	36,0	576,0	1400,0	750	14
26051	30 G 2,5	40,0	864,0	1740,0	750	14
26052	36 G 2,5	44,0	998,0	2050,0	750	14
26053	7 G 4	22,0	269,0	600,0	500	12
26054	4 G 10	22,0	384,0	650,0	500	8
26055	4 G 16	27,0	614,0	1100,0	500	6
26059	5 G 16	34,0	768,0	1600,0	750	6
26056	4 G 25	30,0	960,0	1600,0	500	4
26057	4 G 35	36,0	1344,0	2050,0	1000	2
26058	4 G 50	42,0	1920,0	2800,0	1000	1

Dimensions and specifications may be changed without prior notice. (RG01)