


# Audio

## Speaker cables, coaxial

HELUSOUND®



### Type

#### Cable structure

Conductor material:  
Core insulation:  
Core colours:  
Sheath material:  
Cable external diameter:  
Sheath colour:

#### Electrical data

Conductor resistance, max.:  
Insulation resistance, min.:

#### Technical data

Weight:  
Min. bending radius for laying:  
Operating temperature range min.:  
Operating temperature range max.:  
Copper weight:

#### Part no.

Dimensions and specifications may be changed without prior notice.

#### Application

The coaxial HELUSOUND® speaker cable is protected by a counter-rotating double spiral shield and outer jacket. It is characterized due to the construction, in addition to robustness and good drum reeling, especially by high flexibility and small dimensions.

#### Speaker cable 2x2,5

Copper, bare  
PVC  
Black  
PVC  
approx. 6,8 mm  
black

7,98 Ohm/km  
5 MOhm x km

approx. 84 kg/km  
68 mm  
-25°C  
+70°C  
52,0 kg/km

**400061**

#### Speaker cable 2x4,0

Copper, bare  
PVC  
Black  
PVC  
approx. 7,9 mm  
black

4,95 Ohm/km  
5 MOhm x km

approx. 129 kg/km  
80 mm  
-25°C  
+70°C  
87,0 kg/km

**400062**