


N2XY

Power cable, 0,6/1 kV, higher current carrying capacity



Technical data

- Power distribution cables acc. to DIN VDE 0276-603 / HD 603 S1 / IEC 60502
- **Temperature range**
flexing -5°C to +50°C
fixed installation -40°C to +70°C
- Permissible **operating temperature** at conductor +90°C
- Permissible **short circuit temperature** (short circuit duration max. 5 s) +250°C
- **Nominal voltage**
U₀/U 0,6/1 kV
- **Test voltage**
4 kV
- **Minimum bending radius**
single core 15x outer Ø
multi core 12x outer Ø

Cable structure

- Bare copper conductor, single wire or multi wire acc. to DIN VDE 0295 cl.1 or cl.2 / IEC 60228 cl.1 or cl.2
- Core insulation of cross-linked polyethylene (XLPE) compound type DIX3 acc. to HD 603 S1
- Core identification acc. to DIN VDE 0293-308 / 0276-603
- Cores concentrically stranded
- Outer sheath of PVC compound type DMV6 acc. to HD 603 S1
- Sheath colour: black

Properties

- The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

Tests

- Flame retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2

Highest permissible voltage

- Direct current systems
 - Conductor/conductor 1,8 kV
 - Conductor/earth 0,9 kV
- Alternating current systems
 - Single phase systems both outer conductors insulated 1,4 kV
 - Single phase systems one outer conductor earthed 0,7 kV
- Three phase systems 1,2 kV

Note

- re = round conductor, single wire
- rm = round conductor, multi wire
- sm = sectional conductor, multi wire
- J-version = with GN-YE conductor
- O-version = without GN-YE conductor
- The conductor is metrically constructed (mm²). The AWG designation is approximate and purely informative.

Application

Power distribution cables for use in underground, in water, outdoors, in concrete, indoors, in cable ducts, for power stations, industrial applications and switching systems, as well as in local networks if no mechanical damage is expected. Respecting the permissible operating temperature at the conductor of +90°C permits a higher current carrying capacity than PVC insulated power distribution cables.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

No. cores x cross-sec. mm ²		Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km	J type Part no.	AWG-No.		O type Part no.	AWG-No.	
1 x 16	re	11,5	154,0	242,0	32850	6	-	32862	6	-
1 x 25	rm	12,5	240,0	362,0	32851	4	-	32863	4	-
1 x 35	rm	13,5	336,0	470,0	32852	2	-	32864	2	-
1 x 50	rm	15,5	480,0	620,0	32853	1	-	32865	1	-
1 x 70	rm	17,0	672,0	805,0	32854	2/0	-	32866	2/0	-
1 x 95	rm	19,0	912,0	1108,0	32855	3/0	-	32867	3/0	-
1 x 120	rm	20,5	1152,0	1360,0	32856	4/0	-	32868	4/0	-
1 x 150	rm	23,0	1440,0	1670,0	32857	300 kcmil	-	32869	300 kcmil	-
1 x 185	rm	25,5	1776,0	2050,0	32858	350 kcmil	-	32870	350 kcmil	-
1 x 240	rm	28,5	2304,0	2635,0	32859	500 kcmil	-	32871	500 kcmil	-
1 x 300	rm	30,0	2880,0	3200,0	32860	600 kcmil	-	32872	600 kcmil	-
1 x 400	rm	34,0	3840,0	4150,0	32861	750 kcmil	-	32873	750 kcmil	-
4 x 16	rm	21,5	614,0	1042,0	32874	6	-	32884	6	-
4 x 25	rm	28,0	960,0	1640,0	32875	4	-	32885	4	-
4 x 35	rm	27,5	1344,0	1760,0	32876	2	-	32886	2	-
4 x 50	sm	30,0	1920,0	2350,0	32877	1	-	32887	1	-
4 x 70	sm	34,0	2688,0	3100,0	32878	2/0	-	32888	2/0	-
4 x 95	sm	39,0	3648,0	4250,0	32879	3/0	-	32889	3/0	-
4 x 120	sm	42,5	4608,0	5300,0	32880	4/0	-	32890	4/0	-
4 x 150	sm	47,5	5760,0	6400,0	32881	300 kcmil	-	32891	300 kcmil	-
4 x 185	sm	52,0	7104,0	8500,0	32882	350 kcmil	-	32892	350 kcmil	-
4 x 240	sm	58,0	9216,0	11000,0	32883	500 kcmil	-	32893	500 kcmil	-

Dimensions and specifications may be changed without prior notice. (RQ02)