


# Fibre Optic Breakout Cable robust

HCS

**HELUCOM®**  
AT-VQH(ZN)B2Y



## Cable structure

Core type: Composite buffered  
GRP support element

Strain relief elements: Aramide

Type of armouring: Glass yarns

Outer sheath material: PE

Outer sheath colour: Black

## Temperature range

Laying, min.: -5°C

Laying, max.: +50°C

Operating, min.: -25°C

Operating, max.: +70°C

## Other data

Corrosiveness acc. to EN50267-2-3

Halogen-free acc. to 60754-2

Longitudinally water-tight acc. to

IEC 60794-1-2-F5

UV-resistant

Oil-resistant

Designation	Number of fibres	Fibre type	Fibre category	Number of fibres per core	Outer Ø app. mm	Max. tensile force N	Min. stat. bending radius mm	Max. transverse pressure N / cm	Caloric load app. MJ / m kg / km	Weight app. g / m	Part no.
AT-VQH(ZN)B2Y	2	HCS 200/230	Other	1	11,0	1500	200,0	500	2,10	90,0	<b>801196</b>

Dimensions and specifications may be changed without prior notice.

## Application

This HELUCOM® HCS fibre cable is suitable for fixed installation outdoors. Possible applications are normal and heavy-duty mechanical requirements for example in industrial environments. This is the reason we also equipped the cable with a non-metallic rodent-protection. With the tight buffer construction, direct plug manufacturing, even on site, poses no problems. With a HCS fibre transmission lengths of up to 300m can be achieved.